

Garant**Turning insert, medium machining DNMG, HB7020, Size / quantity:
110404/50****Order data**

Order number	GG2535 110404/50
GTIN	4067263092827
Item class	GGN

Technical description

Cutting speed v_c main application	125 - 280 mm/min
Cutting depth a_p	0.25 - 2.75 mm
Feed f	0.25 - 0.4 mm/rev.
Quantity	50
Contents	250752 HB7020
ISO code indexable insert	DNMG110404
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

DNMG 110404 Grade HB7020

250752 HB7020