

Garant

**Turning insert, medium machining DNMG, HB7020, Size / quantity:
150612/30**

**Order data**

Order number	GG2535 150612/30
GTIN	4067263092896
Item class	GGN

Technical description

Cutting speed v_c main application	125 - 280 mm/min
Contents	250764 HB7020
Cutting depth a_p	0.8 - 3.75 mm
Feed f	0.25 - 0.4 mm/rev.
Quantity	30
ISO code indexable insert	DNMG150612
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

DNMG 150612 Grade HB7020

250764 HB7020