


**CNMG 120412 DNMG, HBT020, Size / quantity: 150608/50****Order data**

Order number	GG2542 150608/50
GTIN	4067263093046
Item class	GGN

Technical description

Cutting speed v_c main application	100 - 200 mm/min
Cutting depth a_p	0.55 - 3.75 mm
Feed f	0.3 - 0.5 mm/rev.
Quantity	50
Contents	250786 HBT020
ISO code indexable insert	DNMG150608
Grade	HBT020
Chip breaker	PR
Type of product	Indexable insert for turning

Accessories

DNMG 150608 Grade HBT020

250786 HBT020