


Garant**Turning insert, medium machining SNMG, HB7020, Size / quantity: 190612/30****Order data**

Order number	GG2544 190612/30
GTIN	4067263093176
Item class	GGN

Technical description

Contents	251236 HB7020
Feed f	0.2 - 0.4 mm/rev.
Cutting speed v_c main application	130 - 280 mm/min
Cutting depth a_p	0.8 - 6.75 mm
Quantity	30
ISO code indexable insert	SNMG190612
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

SNMG 190612 Grade HB7020

251236 HB7020