

Garant**Turning insert, medium machining VBGT, HU7310, Size / quantity: 110302/50****Order data**

Order number	GG2681 110302/50
GTIN	4067263098409
Item class	GGN

Technical description

Contents	261222 HU7310
Cutting depth a_p	0.15 - 1.75 mm
Cutting speed v_c main application	350 - 600 mm/min
Quantity	50
Feed f	0.1 - 0.3 mm/rev.
ISO code indexable insert	VBGT110302
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VBGT 110302 Grade HU7310

261222 HU7310