

Garant**Turning insert, medium machining SNMG, HB7020, Size / quantity: 190616/30****Order data**

Order number	GG2544 190616/30
GTIN	4067263093190
Item class	GGN

Technical description

Cutting depth a_p	1.6 - 6.75 mm
Contents	251238 HB7020
Cutting speed v_c main application	130 - 280 mm/min
Feed f	0.2 - 0.4 mm/rev.
Quantity	30
ISO code indexable insert	SNMG190616
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

SNMG 190616 Grade HB7020

251238 HB7020