

Garant**Turning insert, medium machining VBGT, HU7310, Size / quantity: 110304/30****Order data**

Order number	GG2681 110304/30
GTIN	4067263098416
Item class	GGN

Technical description

Cutting speed v_c main application	350 - 600 mm/min
Contents	261224 HU7310
Feed f	0.1 - 0.3 mm/rev.
Quantity	30
Cutting depth a_p	0.25 - 1.75 mm
ISO code indexable insert	VBGT110304
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VB.T 110304 Grade HU7310

261224 HU7310