

**Garant****Turning insert, medium machining SNMG, HB7020, Size / quantity: 120404/50****Order data**

Order number	GG2544 120404/50
GTIN	4067263093084
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.25 - 4.25 mm
Feed $f$	0.2 - 0.4 mm/rev.
Cutting speed $v_c$ main application	130 - 280 mm/min
Quantity	50
Contents	251222 HB7020
ISO code indexable insert	SNMG120404
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

SNMG 120404 Grade HB7020

251222 HB7020