

**Garant****Turning insert, roughing SNMG, HB7020, Size / quantity: 120412/50**

## Order data

Order number	GG2549 120412/50
GTIN	4067263093282
Item class	GGN

## Technical description

Cutting speed $v_c$ main application	105 - 260 mm/min
Cutting depth $a_p$	0.8 - 4.25 mm
Feed $f$	0.3 - 0.5 mm/rev.
Quantity	50
Contents	251326 HB7020
ISO code indexable insert	SNMG120412
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

## Accessories

SNMG 120412 Grade HB7020

251326 HB7020