

Garant**Turning insert, medium machining VCGT, HU7310, Size / quantity: 160408/50****Order data**

Order number	GG2686 160408/50
GTIN	4067263098669
Item class	GGN

Technical description

Quantity	50
Cutting speed v_c main application	350 - 600 mm/min
Cutting depth a_p	0.55 - 2.5 mm
Contents	261459 HU7310
Feed f	0.1 - 0.3 mm/rev.
ISO code indexable insert	VCGT160408
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VC.T 160408 Grade HU7310

261459 HU7310