

**Value pack turning insert roughing SNMG****Order data**

Order number	GG2549 190616/30
GTIN	4067263093336
Item class	GGN

Technical description

Contents	251336 HB7020
Cutting speed v_c main application	105 - 260 mm/min
Feed f	0.3 - 0.5 mm/rev.
Cutting depth a_p	1.05 - 6.75 mm
Quantity	30
ISO code indexable insert	SNMG190616
Type	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG2549-190616/30>