

Garant**Turning insert, medium machining VCGT, HB7310, Size / quantity: 160402/30****Order data**

Order number	GG2689 160402/30
GTIN	4067263098713
Item class	GGN

Technical description

Cutting speed v_c main application	250 - 600 mm/min
Contents	261457 HB7310
Cutting depth a_p	0.15 - 2.5 mm
Feed f	0.1 - 0.3 mm/rev.
Quantity	30
ISO code indexable insert	VCGT160402
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VCGT 160402 Grade HB7310

261457 HB7310