

Garant**Turning insert, medium machining TNMG, HB7020, Size / quantity: 160408/50****Order data**

Order number	GG2555 160408/50
GTIN	4067263093428
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 4 mm
Feed f	0.2 - 0.4 mm/rev.
Cutting speed v_c main application	130 - 280 mm/min
Quantity	50
Contents	251544 HB7020
ISO code indexable insert	TNMG160408
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

TNMG 160408 Grade HB7020

251544 HB7020