

**Garant****Turning insert, roughing SNMG, HB7020, Size / quantity: 190624/50****Order data**

Order number	GG2549 190624/50
GTIN	4067263093367
Item class	GGN

**Technical description**

Feed f	0.3 - 0.5 mm/rev.
Cutting speed $v_c$ main application	105 - 260 mm/min
Cutting depth $a_p$	1.6 - 6.75 mm
Quantity	50
Contents	251338 HB7020
ISO code indexable insert	SNMG190624
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

## Accessories

SNMG 190624 Grade HB7020

251338 HB7020