


**Turning insert, medium machining TNMG, HBT020, Size / quantity: 160408/50****Order data**

Order number	GG2558 160408/50
GTIN	4067263093466
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	120 - 240 mm/min
Feed $f$	0.2 - 0.3 mm/rev.
Cutting depth $a_p$	0.55 - 4 mm
Quantity	50
Contents	251565 HBT020
ISO code indexable insert	TNMG160408
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

**Accessories**

TNMG 160408 Grade HBT020

251565 HBT020