

Garant**Turning insert, roughing SNMG, HB7020, Size / quantity: 190624/30**

Order data

Order number	GG2549 190624/30
GTIN	4067263093350
Item class	GGN

Technical description

Cutting speed v_c main application	105 - 260 mm/min
Cutting depth a_p	1.6 - 6.75 mm
Feed f	0.3 - 0.5 mm/rev.
Contents	251338 HB7020
Quantity	30
ISO code indexable insert	SNMG190624
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

SNMG 190624 Grade HB7020

251338 HB7020