

Garant**Turning insert, roughing SNMG, HB7020, Size / quantity: 150616/50**

Order data

Order number	GG2549 150616/50
GTIN	4067263093329
Item class	GGN

Technical description

Feed f	0.3 - 0.5 mm/rev.
Cutting speed v_c main application	105 - 260 mm/min
Cutting depth a_p	1.05 - 5.25 mm
Quantity	50
Contents	251332 HB7020
ISO code indexable insert	SNMG150616
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

SNMG 150616 Grade HB7020

251332 HB7020