

## Garant

### GARANT Softcut® 90° shoulder mill MTC, with bore, Ø D / Z<sub>eff</sub>: 63/5mm



#### Order data

Order number	215161 63/5
GTIN	4045197455239
Item class	210

#### Description

##### Version:

High precision square shoulder milling cutter with irregular pitch for very smooth cutting, very high precision and cutting power. High performance indexable square shoulder milling cutter **with special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or **for spindles with low drive power**.

##### Application:

For corner milling to large depths, also slotting. General use in all steels including stainless steels. Especially for **MTC (Multi Task Cutting)** use on the new generation of turning / milling centres (MTM).

##### Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**. The insert pocket must be modified when using indexable inserts with a radius greater than 3.1 mm.

#### Technical description

Pack of insert screws	219808 (15IP; 3.8 Nm)
Number of effective inserts Z <sub>eff</sub>	5

suitable indexable insert	AP.. 1805..
Overall length $L_{tot}$	50 mm
Mounting bore $\varnothing$	27 mm
maximum cutting depth $a_{p\ max}$	28 mm
Cutting edge $\varnothing D_c$	63 mm
Series	Softcut®
Number of indexable inserts	10
Shank type	with bore
Setting angle $\kappa$	90 degrees
Milling application	Corner milling
Milling application	Ramping
Milling application	Circular milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

## Accessories

Set of insert screws 10-piece	219808
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8