


**Turning insert, medium machining TNMG, HBT020, Size / quantity: 160404/30****Order data**

Order number	GG2558 160404/30
GTIN	4067263093435
Item class	GGN

Technical description

Cutting speed v_c main application	120 - 240 mm/min
Feed f	0.2 - 0.3 mm/rev.
Contents	251564 HBT020
Cutting depth a_p	0.25 - 4 mm
Quantity	30
ISO code indexable insert	TNMG160404
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

TNMG 160404 Grade HBT020

251564 HBT020