

Garant**Turning insert, medium machining VNMG, HB7020, Size / quantity: 160408/50****Order data**

Order number	GG2561 160408/50
GTIN	4067263843788
Item class	GGN

Technical description

Cutting speed v_c main application	110 - 280 mm/min
Cutting depth a_p	0.55 - 2.5 mm
Feed f	0.2 - 0.4 mm/rev.
Quantity	50
Contents	251804 HB7020
ISO code indexable insert	VNMG160408
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

VNMG 160408 Grade HB7020

251804 HB7020