

Garant**Turning insert, roughing WNMG, HB7020, Size / quantity: 080408/30****Order data**

Order number	GG2568 080408/30
GTIN	4067263093718
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 2.75 mm
Contents	252208 HB7020
Cutting speed v_c main application	85 - 260 mm/min
Feed f	0.3 - 0.5 mm/rev.
Quantity	30
ISO code indexable insert	WNMG080408
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

WNMG 080408 Grade HB7020

252208 HB7020