

Garant**Turning insert, roughing WNMG, HB7020, Size / quantity: 080412/50****Order data**

Order number	GG2568 080412/50
GTIN	4067263093749
Item class	GGN

Technical description

Cutting speed v_c main application	85 - 260 mm/min
Cutting depth a_p	0.8 - 2.75 mm
Feed f	0.3 - 0.5 mm/rev.
Quantity	50
Contents	252210 HB7020
ISO code indexable insert	WNMG080412
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

WNMG 080412 Grade HB7020

252210 HB7020