



## Value pack turning insert roughing CNMG



### Order data

Order number	GG2576 160612/30
GTIN	4067263094210
Item class	GGN

### Technical description

Cutting depth $a_p$	0.8 - 5.5 mm
Contents	250221 HBT130
Quantity	30
Cutting speed $v_c$ main application	70 - 120 mm/min
Feed $f$	0.3 - 0.5 mm/rev.
ISO code indexable insert	CNMG160612
Type	HBT130
Chip breaker	MR
Type of product	Indexable insert for turning

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG2576-160612/30>

