

**Turning insert, roughing CNMG, HBT130, Size / quantity: 120408/50****Order data**

Order number	GG2576 120408/50
GTIN	4067263094166
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 4.25 mm
Cutting speed v_c main application	70 - 120 mm/min
Quantity	50
Feed f	0.3 - 0.5 mm/rev.
Contents	250218 HBT130
ISO code indexable insert	CNMG120408
Grade	HBT130
Chip breaker	MR
Type of product	Indexable insert for turning

Accessories

CNMG 120408 Grade HBT130

250218 HBT130