



**Turning insert, medium machining DNMG, HBT130, Size / quantity:
110408/30**



Order data

Order number	GG2579 110408/30
GTIN	4067263094357
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 2.75 mm
Feed f	0.2 - 0.3 mm/rev.
Contents	250781 HBT130
Cutting speed v_c main application	80 - 135 mm/min
Quantity	30
ISO code indexable insert	DNMG110408
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

DNMG 110408 Grade HBT130

250781 HBT130