

Garant**Turning insert, roughing DNMG, HB7130-2, Size / quantity: 150612/50****Order data**

| | |
|--------------|------------------|
| Order number | GG2580 150612/50 |
| GTIN | 4067263094425 |
| Item class | GGN |

Technical description

| | |
|--------------------------------------|------------------------------|
| Feed f | 0.35 - 0.45 mm/rev. |
| Cutting depth a_p | 0.8 - 3.75 mm |
| Contents | 250864 HB7130-2 |
| Cutting speed v_c main application | 90 - 170 mm/min |
| Quantity | 50 |
| ISO code indexable insert | DNMG150612 |
| Grade | HB7130-2 |
| Chip breaker | VG |
| Type of product | Indexable insert for turning |

Accessories

DNMG 150612 Grade HB7130-2

250864 HB7130-2