

**Garant**

**Turning insert, medium machining KNUX, HB7020, Size / quantity:  
160405L/50**

**Order data**

Order number	GG2541 160405L/50
GTIN	4067263094586
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	120 - 250 mm/min
Feed $f$	0.2 - 0.5 mm/rev.
Cutting depth $a_p$	0.35 - 4 mm
Quantity	50
Contents	251032 HB7020
ISO code indexable insert	KNUX160405
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

**Accessories**

KNUX 160405L Grade HB7020	251032 HB7020
---------------------------	---------------