

Garant

**Turning insert, medium machining KNUX, HB7020, Size / quantity:
160410R/50**

**Order data**

Order number	GG2541 160410R/50
GTIN	4067263094609
Item class	GGN

Technical description

Cutting depth a_p	0.65 - 4 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting speed v_c main application	120 - 250 mm/min
Quantity	50
Contents	251036 HB7020
ISO code indexable insert	KNUX160410
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

KNUX 160410R Grade HB7020	251036 HB7020
---------------------------	---------------