

**Garant****Turning insert, medium machining CCMT, HB7020, Size / quantity: 09T304/30****Order data**

Order number	GG2620 09T304/30
GTIN	4067263095194
Item class	GGN

**Technical description**

Feed f	0.1 - 0.25 mm/rev.
Cutting depth $a_p$	0.25 - 3.25 mm
Cutting speed $v_c$ main application	130 - 280 mm/min
Contents	260150 HB7020
Quantity	30
ISO code indexable insert	CCMT09T304
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

CC.T 09T304 Grade HB7020

260150 HB7020