

Garant**Turning insert, medium machining DCMT, HB7020, Size / quantity: 070204/50****Order data**

Order number	GG2624 070204/50
GTIN	4067263095422
Item class	GGN

Technical description

Cutting speed v_c main application	130 - 280 mm/min
Feed f	0.1 - 0.25 mm/rev.
Cutting depth a_p	0.25 - 1.75 mm
Contents	260452 HB7020
Quantity	50
ISO code indexable insert	DCMT070204
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

DC.T 070204 Grade HB7020

260452 HB7020