

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 26×20G, Height mm / number of drawers: 1000/7A**Order data**

Order number	930605 1000/7A
GTIN	4067263100669
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 30×24G, with drawers 26×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Height	1000 mm
Width	750 mm
Base cabinet underneath height-adjustable workstation	no

Usable height for drawers	900 mm
Drawer usable area in G	26×20
Drawer usable width in G	26
Electronic locking system can be retrofitted	yes
Number of doors	0
Number of pull-out shelves	0
Drawer usable depth in G	20
Weight	125 kg
Drawer usable width	650 mm
Usable height	900 mm
Number of drawers	7
Depth	600 mm
Drawer usable depth	500 mm
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26×20G
Type of product	Tool cabinet