

Garant**Turning insert, medium machining DCMT, HB7020, Size / quantity: 11T302/30****Order data**

Order number	GG2624 11T302/30
GTIN	4067263095439
Item class	GGN

Technical description

Feed f	0.1 - 0.25 mm/rev.
Cutting speed v_c main application	130 - 280 mm/min
Contents	260458 HB7020
Cutting depth a_p	0.15 - 2.75 mm
Quantity	30
ISO code indexable insert	DCMT11T302
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

DC.T 11T302 Grade HB7020

260458 HB7020