

**Garant****Turning insert, medium machining TCMT, HB7020, Size / quantity: 16T304/50****Order data**

Order number	GG2632 16T304/50
GTIN	4067263095767
Item class	GGN

**Technical description**

Feed f	0.1 - 0.25 mm/rev.
Cutting speed $v_c$ main application	130 - 280 mm/min
Cutting depth $a_p$	0.25 - 4 mm
Contents	260986 HB7020
Quantity	50
ISO code indexable insert	TCMT16T304
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

**Accessories**

TC.T 16T304 Grade HB7020

260986 HB7020