


**Turning insert, medium machining TCMT, HBT020, Size / quantity: 16T304/30****Order data**

|              |                  |
|--------------|------------------|
| Order number | GG2635 16T304/30 |
| GTIN         | 4067263095811    |
| Item class   | GGN              |

**Technical description**

|                                      |                              |
|--------------------------------------|------------------------------|
| Cutting speed $v_c$ main application | 120 - 240 mm/min             |
| Cutting depth $a_p$                  | 0.25 - 4 mm                  |
| Feed $f$                             | 0.2 - 0.3 mm/rev.            |
| Contents                             | 261018 HBT020                |
| Quantity                             | 30                           |
| ISO code indexable insert            | TCMT16T304                   |
| Grade                                | HBT020                       |
| Chip breaker                         | PM                           |
| Type of product                      | Indexable insert for turning |

**Accessories**

TCMT 16T304 Grade HBT020

261018 HBT020