

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 20×24G, Height mm / number of drawers: 1000/7A**Order data**

Order number	931005 1000/7A
GTIN	4067263100805
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 24×28G, with drawers 20×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Drawer usable depth	600 mm
Usable height for drawers	900 mm
Number of pull-out shelves	0

Drawer usable depth in G	24
Drawer usable area in G	20×24
Number of drawers	7
Base cabinet underneath height-adjustable workstation	no
Drawer usable width	500 mm
Depth	700 mm
Usable height	900 mm
Drawer usable width in G	20
Width	600 mm
Weight	123 kg
Height	1000 mm
Number of doors	0
Electronic locking system can be retrofitted	yes
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×24G
Type of product	Tool cabinet