

Garant GRIDLINE

Tool cabinet complete with drawers 200 kg, 26×24G, Height mm / number of drawers: 1250/10A**Order data**

Order number	931115 1250/10A
GTIN	4067263100980
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Usable height for drawers	1150 mm
Number of doors	0

Depth	700 mm
Weight	197 kg
Base cabinet underneath height-adjustable workstation	no
Drawer usable depth in G	24
Drawer usable width in G	26
Usable height	1150 mm
Electronic locking system can be retrofitted	yes
Drawer usable width	650 mm
Drawer usable depth	600 mm
Width	750 mm
Number of drawers	10
Number of pull-out shelves	0
ComfortClose	no
Ribbed rubber inlay with anti-roll lip on 3 sides	no
Height	1250 mm
Drawer usable area in G	26×24
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26×24G
Type of product	Tool cabinet