


**Turning insert, medium machining TCMT, HBT020, Size / quantity: 16T304/50****Order data**

Order number	GG2635 16T304/50
GTIN	4067263095828
Item class	GGN

Technical description

Cutting depth a_p	0.25 - 4 mm
Feed f	0.2 - 0.3 mm/rev.
Contents	261018 HBT020
Cutting speed v_c main application	120 - 240 mm/min
Quantity	50
ISO code indexable insert	TCMT16T304
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

TCMT 16T304 Grade HBT020

261018 HBT020