

**HOLEX****Turning insert, medium machining VBMT, HBT020, Size / quantity: 110304/50****Order data**

Order number	GG2639 110304/50
GTIN	4067263095927
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.25 - 1.75 mm
Feed $f$	0.2 - 0.3 mm/rev.
Contents	261252 HBT020
Cutting speed $v_c$ main application	120 - 240 mm/min
Quantity	50
ISO code indexable insert	VBMT110304
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

## Accessories

VBMT 110304 Grade HBT020

261252 HBT020