




Centring vice, Width: 120Amm



Order data

Order number	363300 120A
GTIN	4067263101116
Item class	30N

Description

Version:

- **Very good accessibility and perfectly symmetrical.**
- **Fully plasma-nitrided and precision milled on the underside.**
- **Clamps raw materials and finished parts with the least possible backstroke of the jaws / component.**
- **The clamping range can be changed by reversing the jaws.**

Supplied with GARANT ZeroClamp adaptation with 80 mm pitch.

Includes 4 ZeroClamp clamping studs.

Application:

Perfect for 5-face machining. Centred clamping.

Suitable for:

Top jaws No. 363310 – 363324.

Supplied with:

Base body, spindle, spindle nuts and four clamping studs suitable for automation extension base No. 360164 XP80Z.

Optional extras:

Torque wrench No. 656050, hexagon socket No. 642229 13, assembly station No. 358595 80.

Note:

Suitable for the GARANT Turntable automation system in combination with / for automation extension base No. 360164 XP80Z. Suitable top jaws No. 363310 – 363324 are not included in the scope of supply. Clamping situation S2 arises by reversing the jaws.

Technical description

Weight	7.6 kg
L	180 mm
B	120 mm
Reference dimension	80 mm
maximum clamping force	28 kN
Version	Zero-point clamping system
Height H	59 mm
maximum tightening torque	100 Nm
Colour code	HOLEX ZS 120
Type of product	Machine vice