

Garant**Turning insert, medium machining VCMT, HB7020, Size / quantity: 160408/50****Order data**

Order number	GG2640 160408/50
GTIN	4067263096023
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 2.5 mm
Feed f	0.1 - 0.25 mm/rev.
Contents	261459 HB7020
Cutting speed v_c main application	130 - 280 mm/min
Quantity	50
ISO code indexable insert	VCMT160408
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

VC.T 160408 Grade HB7020

261459 HB7020