

**HOLEX****Turning insert, medium machining VCMT, HBT020, Size / quantity: 160408/30****Order data**

Order number	GG2643 160408/30
GTIN	4067263096078
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	120 - 240 mm/min
Contents	261476 HBT020
Cutting depth $a_p$	0.55 - 2.5 mm
Feed $f$	0.2 - 0.3 mm/rev.
Quantity	30
ISO code indexable insert	VCMT160408
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

## Accessories

VCMT 160408 Grade HBT020

261476 HBT020