

Garant**Turning insert, medium machining VCMT, HB7020, Size / quantity: 110304/30****Order data**

Order number	GG2640 110304/30
GTIN	4067263095972
Item class	GGN

Technical description

Cutting speed v_c main application	130 - 280 mm/min
Contents	261454 HB7020
Cutting depth a_p	0.25 - 1.75 mm
Feed f	0.1 - 0.25 mm/rev.
Quantity	30
ISO code indexable insert	VCMT110304
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

VC.T 110304 Grade HB7020

261454 HB7020