

**HOLEX****Turning insert, medium machining VBMT, HBT020, Size / quantity: 160404/50****Order data**

Order number	GG2639 160404/50
GTIN	4067263095941
Item class	GGN

**Technical description**

Feed f	0.2 - 0.3 mm/rev.
Cutting speed $v_c$ main application	120 - 240 mm/min
Contents	261257 HBT020
Cutting depth $a_p$	0.25 - 2.5 mm
Quantity	50
ISO code indexable insert	VBMT160404
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

## Accessories

VBMT 160404 Grade HBT020

261257 HBT020