

**Turning insert, medium machining DCMT, HBT130, Size / quantity: 11T302/50****Order data**

Order number	GG2651 11T302/50
GTIN	4067263096566
Item class	GGN

Technical description

Feed f	0.2 - 0.3 mm/rev.
Cutting speed v_c main application	80 - 135 mm/min
Cutting depth a_p	0.15 - 2.75 mm
Contents	260503 HBT130
Quantity	50
ISO code indexable insert	DCMT11T302
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

DCMT 11T302 Grade HBT130

260503 HBT130