

**Turning insert, medium machining TCMT, HBT130, Size / quantity: 16T304/50****Order data**

Order number	GG2659 16T304/50
GTIN	4067263096962
Item class	GGN

Technical description

Contents	261018 HBT130
Feed f	0.2 - 0.3 mm/rev.
Cutting depth a_p	0.25 - 4 mm
Cutting speed v_c main application	80 - 135 mm/min
Quantity	50
ISO code indexable insert	TCMT16T304
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

TCMT 16T304 Grade HBT130

261018 HBT130