

**Turning insert, medium machining TCMT, HBT130, Size / quantity: 16T308/50****Order data**

Order number	GG2659 16T308/50
GTIN	4067263096986
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	80 - 135 mm/min
Cutting depth $a_p$	0.55 - 4 mm
Feed $f$	0.2 - 0.3 mm/rev.
Contents	261019 HBT130
Quantity	50
ISO code indexable insert	TCMT16T308
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

**Accessories**

TCMT 16T308 Grade HBT130

261019 HBT130