

**HOLEX****Turning insert, medium machining VCMT, HBT130, Size / quantity: 160404/50****Order data**

Order number	GG2667 160404/50
GTIN	4067263097303
Item class	GGN

**Technical description**

Contents	261474 HBT130
Cutting speed $v_c$ main application	80 - 135 mm/min
Feed $f$	0.2 - 0.3 mm/rev.
Cutting depth $a_p$	0.25 - 2.5 mm
Quantity	50
ISO code indexable insert	VCMT160404
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

## Accessories

VCMT 160404 Grade HBT130

261474 HBT130