

**Turning insert, medium machining VCMT, HBT130, Size / quantity: 110304/50****Order data**

Order number	GG2667 110304/50
GTIN	4067263097280
Item class	GGN

Technical description

Feed f	0.2 - 0.3 mm/rev.
Cutting speed v_c main application	80 - 135 mm/min
Cutting depth a_p	0.25 - 1.75 mm
Contents	261472 HBT130
Quantity	50
ISO code indexable insert	VCMT110304
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

VCMT 110304 Grade HBT130

261472 HBT130