

**Turning insert, medium machining VBMT, HBT130, Size / quantity: 110304/50****Order data**

Order number	GG2663 110304/50
GTIN	4067263097068
Item class	GGN

Technical description

Contents	261252 HBT130
Cutting speed v_c main application	80 - 135 mm/min
Feed f	0.2 - 0.3 mm/rev.
Cutting depth a_p	0.25 - 1.75 mm
Quantity	50
ISO code indexable insert	VBMT110304
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

VBMT 110304 Grade HBT130

261252 HBT130