

**Turning insert, medium machining VCMT, HBT130, Size / quantity: 160408/50****Order data**

Order number	GG2667 160408/50
GTIN	4067263097327
Item class	GGN

Technical description

Feed f	0.2 - 0.3 mm/rev.
Contents	261476 HBT130
Cutting speed v_c main application	80 - 135 mm/min
Cutting depth a_p	0.55 - 2.5 mm
Quantity	50
ISO code indexable insert	VCMT160408
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

VCMT 160408 Grade HBT130

261476 HBT130